


Inductive sensor

IDE2060-ARKG/FIXE

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	60; (fixed: 60)
Housing	rectangular
Dimensions [mm]	105 x 80 x 40

Electrical data

Operating voltage [V]	10...55 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.5
Minimum load current [mA]	4
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	4
Short-circuit protection	yes
Type of short-circuit protection	pulsed



Inductive sensor

IDE2060-ARKG/FIXE

Overload protection	yes
---------------------	-----

Detection zone

Sensing range	[mm]	60; (fixed: 60)
Real sensing range S_r	[mm]	$60 \pm 10 \%$
Operating distance	[mm]	0...48.6

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection	IP 65	

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	rectangular	
Mounting	non-flush mountable	
Dimensions	[mm]	105 x 80 x 40
Materials	PPE modified	

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied	screwdriver: 1	
----------------	----------------	--

Remarks

Pack quantity	1 pcs.	
---------------	--------	--

Electrical connection

terminals: ...2.5 mm²; Cable sheath: Ø 7...13 mm

Connection

