


Inductive sensor

IEK3001-BPOG/US-100-DPS

Article no longer available - archive entry

Alternative articles: IE5219

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1
Housing	threaded type
Dimensions [mm]	M8 x 1

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes

IE5250



Inductive sensor

IEK3001-BPOG/US-100-DPS

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone	
Sensing range [mm]	1
Real sensing range S_r [mm]	$1 \pm 10\%$
Operating distance [mm]	0...0.8

Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data	
Housing	threaded type
Mounting	flush mountable
Dimensions [mm]	M8 x 1
Thread designation	M8 x 1
Materials	housing: brass white bronze coated; sensing face: PBT

Displays / operating elements		
Display	switching status	1 x LED, yellow

Аксессуары	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



IE5250



Inductive sensor

IEK3001-BPOG/US-100-DPS

Connection

