

IE5294




Inductive sensor

IEB3002-BPKG/V4A

Article no longer available - archive entry

Alternative articles: IE5295
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics	
Electrical design	PNP
Output function	normally open
Sensing range [mm]	2
Housing	threaded type
Dimensions [mm]	M8 x 1
Electrical data	
Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	yes
Outputs	
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	yes

IE5294



Inductive sensor

IEB3002-BPKG/V4A

Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1
Thread designation		M8 x 1
Materials		stainless steel (1.4571/316Ti); POM
Аксессуары		
Items supplied		lock nuts: 2
Remarks		
Remarks		IP 67 if screwed on
Pack quantity		1 pcs.

IE5294



Inductive sensor

IEB3002-BPKG/V4A

Electrical connection

Cable: 2 m, PUR; 3 x 0.14 mm²

Connection



BK =	Core colours :
BN =	black
BU =	brown
	blue