


Inductive sensor

IEB3002-APKG/V4A/AS

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	2
Housing	threaded type
Dimensions [mm]	M8 x 1

Electrical data

Operating voltage [V]	10...36 DC; (; to PELV)
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

IE5321



Inductive sensor

IEB3002-APKG/V4A/AS

Detection zone		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67; (if screwed on)
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1
Thread designation		M8 x 1
Materials		stainless steel; sensing face: LCP
Displays / operating elements		
Display	switching status	4 x 90° LED, yellow
Аксессуары		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M8; coding: A		

IE5321

Inductive sensor

IEB3002-APKG/V4A/AS



Connection

