


Inductive sensor

IEBC005-ASKG/0,3M/US



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	5
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 37

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10; (only in 3-wire operation)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.8
Minimum load current [mA]	2; (only in 2-wire operation)
Max. leakage current [mA]	0.5; (only in 2-wire operation)
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	700
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	5
Real sensing range S_r [mm]	$5 \pm 10 \%$
Operating distance [mm]	0...4.05



Inductive sensor

IEBC005-ASKG/0,3M/US

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
MTTF	[ANN]	2988
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	File number UL	E174191
Mechanical data		
Weight	[g]	30.5
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1 / L = 37
Thread designation		M8 x 1
Materials		brass white bronze coated; sensing face: LCP
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.

IE5352



Inductive sensor

IEBC005-ASKG/0,3M/US

Electrical connection - plug

Cable: 0.3 m, PVC; 3 x 0.14 mm²

Connector: 1 x M12; coding: A; Locking: rotatable

