


Inductive sensor

IEB21,5-BRKG/0,5M

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally closed
Sensing range [mm]	1.5
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 37

Electrical data

Operating voltage [V]	10...30 DC
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.8
Max. leakage current [mA]	0.4
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	1.5
Real sensing range S_r [mm]	$1.5 \pm 10\%$
Operating distance [mm]	0...1.2

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10

Operating conditions

Ambient temperature [°C]	0...60
Protection	IP 67



IE5374



Inductive sensor

IEB21,5-BRKG/0,5M

Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Weight	[g]	30.6
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 37
Thread designation		M8 x 1
Materials		brass white bronze coated; sensing face: LCP
Tightening torque	[Nm]	A = 5 mm: 1,5 Nm; B: 2 Nm
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 0.5 m, PPU; 2 x 0.14 mm ²		
Connection		



BN = Core colours :
brown
BU = blue

IE5374



Inductive sensor

IEB21,5-BRKG/0,5M

Diagrams and graphs

Installation

