




Inductive sensor

IEB3002BAPKG/0,8M/FH/AS



Product characteristics		
Electrical design		PNP
Output function		normally closed
Sensing range	[mm]	2
Housing		threaded type
Dimensions	[mm]	M8 x 1 / L = 35
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally closed
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Short-time current rating of switching output	[mA]	200
Switching frequency DC	[Hz]	850
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	1...15

IE5388



Inductive sensor

IEB3002BAPKG/0,8M/FH/AS

Switch point drift	[X01]	-10...10
--------------------	-------	----------

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[ANN]	2826

Mechanical data

Weight	[g]	32.1
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 35
Thread designation		M8 x 1
Materials		brass white bronze coated; LCP

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Cable: 0.8 m, PUR; flame-retardant (FRNC); 3 x 0.14 mm²

Connector: 1 x M8; coding: A



Connection

