


IES225



Inductive sensor

IEB2003BBRKG/V4A/AS



Product characteristics

Electrical design	PNP/NPN
Output function	normally closed
Sensing range [mm]	3
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 30

Application

Special feature	Gold-plated contacts; Increased sensing range
Application	Підходить для промислового застосування, рухомої техніки та технологій охолодження та змащення; Industrial applications / factory automation

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Max. leakage current [mA]	0.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	800
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	3
Real sensing range S_r [mm]	$3 \pm 10 \%$
Operating distance [mm]	0...2.43
Increased sensing range	yes

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis [X01]	1...15



Inductive sensor

IEB2003BBRKG/V4A/AS

Switch point drift	[X01]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-40...85	
Protection		IP 65; IP 66; IP 67; IP 68; IP 69K; (with ifm socket duly screwed on)	
Tests / approvals			
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	10 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
	EN 55011	class B	
Vibration resistance	EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes	
Shock resistance	EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes	
Continuous shock resistance	EN 60068-2-27	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes	
Fast temperature change	EN 60068-2-14 Na	TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles	
Salt spray test	EN 60068-2-52 Kb	severity level 5 (4 test cycles)	
MTTF	[ANN]	1708	
Embedded software included		yes	
UL approval	Ta	-25...80 °C	
	Enclosure type	Type 1	
	подача напруги	Limited Voltage/Current	
	UL Approval no.	A017	
	File number UL	E174191	
Mechanical data			
Weight	[g]	3.1	
Housing		threaded type	
Mounting		flush mountable	
Dimensions	[mm]	M8 x 1 / L = 30	
Thread designation		M8 x 1	
Materials		stainless steel (1.4404 / 316L); sensing face: LCP white; LED window: PEI; lock nuts: stainless steel (1.4404 / 316L)	
Tightening torque	[Nm]	A = 5 mm: 2 Nm; B: 5 Nm	
Displays / operating elements			
Display		switching status	4 x 90° LED, yellow
Аксессуары			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	



Inductive sensor

IEB2003BBRKG/V4A/AS

Electrical connection



Connection



Electrical connection - plug

Connector: 1 x M8; Contacts: gold-plated

Diagrams and graphs

Installation

