


Inductive sensor

IEB3001-APOG/PPU

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	1
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 35

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	750
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	1
Real sensing range S_r [mm]	$1 \pm 10\%$
Operating distance [mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Mechanical data

Housing	threaded type
---------	---------------

IE5217



Inductive sensor

IEB3001-APOG/PPU

Mounting	flush mountable
Dimensions [mm]	M8 x 1 / L = 35
Thread designation	M8 x 1
Materials	brass nickel-plated; sensing face: PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied	lock nuts: 2
----------------	--------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PUR / PVC; 3 x 0.14 mm²

Connection



BN = Core colours :
brown
BU = blue
BK = black