




Inductive sensor

IEB3002,5BPOG/AS-510-TPS

Article no longer available - archive entry

Alternative articles: IE5292

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	2.5
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 50

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	15; (24 V)
Reverse polarity protection	no

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	2.5
Real sensing range Sr [mm]	2.5 ± 10 %
Operating distance [mm]	2.03

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10

Operating conditions

Ambient temperature [°C]	0...60
--------------------------	--------

IE5245




Inductive sensor

IEB3002,5BPOG/AS-510-TPS

Protection	IP 65	
Mechanical data		
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions [mm]	M8 x 1 / L = 50	
Thread designation	M8 x 1	
Materials	housing: brass nickel-plated; sensing face: PBT	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	

Electrical connection - plug

Connector: 1 x M8; coding: A



Connection

