

IE5272




Inductive sensor

IEB3002-BPOG/V4A/10M

Article no longer available - archive entry

Alternative articles: IE5287
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	2
Housing		threaded type
Dimensions	[mm]	M8 x 1
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 15
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	2000
Short-circuit protection		yes

IE5272



Inductive sensor

IEB3002-BPOG/V4A/10M

Type of short-circuit protection	pulsed	
Overload protection	yes	
Detection zone		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	3...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 65	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M8 x 1
Thread designation	M8 x 1	
Materials	stainless steel (1.4571/316Ti); PC	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	

IE5272




Inductive sensor

IEB3002-BPOG/V4A/10M

Electrical connection

Cable: 10 m, PVC; 3 x 0.14 mm²

Connection



BK =	Core colours :
BN =	black
BU =	brown
	blue