

IE5276




Inductive sensor

IEB3001,5-ANOG/PH

Article no longer available - archive entry

Alternative articles: IE5313
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		NPN
Output function		normally open
Sensing range	[mm]	1.5
Housing		threaded type
Dimensions	[mm]	M8 x 1
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 10
Reverse polarity protection		no
Outputs		
Electrical design		NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	2000
Short-circuit protection		no
Overload protection		no


IE5276



Inductive sensor

IEB3001,5-ANOG/PH

Detection zone		
Sensing range	[mm]	1.5
Real sensing range Sr	[mm]	1.5 ± 10 %
Operating distance	[mm]	0...1.2
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	3...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1
Thread designation		M8 x 1
Materials		brass nickel-plated
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; highly flexible; 3 x 0.14 mm ²		
Connection		



Core colours :
BK = black
BN = brown
BU = blue