




Inductive sensor

IEB31,5-BPKG/AS-514-TPS

Article no longer available - archive entry

Alternative articles: IE5412

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1.5
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 32.5

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	10; (24 V)
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	no

Detection zone

Sensing range [mm]	1.5
Real sensing range S_r [mm]	$1.5 \pm 10 \%$
Operating distance [mm]	0...1.2

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
-------------------	---

IE5347



Inductive sensor

IEB31,5-BPKG/AS-514-TPS

Hysteresis	[X01]	< 15
Switch point drift	[X01]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 32.5
Thread designation		M8 x 1
Materials		housing: stainless steel; sensing face: PBT

Displays / operating elements

Display	switching status	4 x 90° LED, yellow
---------	------------------	---------------------

Аксессуары

Items supplied		lock nuts: 2
----------------	--	--------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



Connection

