

IE5361




Inductive sensor

IEB3004-BPKG/V4A/AS-514-TPS RT

Article no longer available - archive entry

Alternative articles: IE5362

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	4
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 50

Electrical data

Operating voltage [V]	10...36 DC; (; to PELV)
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	300
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	4
Operating distance [mm]	0...3.25

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
-------------------	---

IE5361



Inductive sensor

IEB3004-BPKG/V4A/AS-514-TPS RT

Hysteresis	[X01]	1...20
------------	-------	--------

Operating conditions

Ambient temperature	[°C]	-10...60
---------------------	------	----------

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B

Mechanical data

Housing	threaded type
---------	---------------

Mounting	non-flush mountable
----------	---------------------

Dimensions	[mm]	M8 x 1 / L = 50
------------	------	-----------------

Thread designation	M8 x 1
--------------------	--------

Materials	stainless steel; LCP
-----------	----------------------

Displays / operating elements

Display	switching status	4 x 90° LED, red
---------	------------------	------------------

Аксессуары

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Remarks	IP 67 if screwed on
---------	---------------------

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



IE5361



Inductive sensor

IEB3004-BPKG/V4A/AS-514-TPS RT

Connection

