

IF5266




Inductive sensor

IFB3004-BPKG/MS

Article no longer available - archive entry

Alternative articles: IF5249
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	4
Housing		threaded type
Dimensions	[mm]	M12 x 1
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	125; (150 (...50 °C))
Switching frequency DC	[Hz]	400
Short-circuit protection		yes
Type of short-circuit protection		pulsed

IF5266



Inductive sensor

IFB3004-BPKG/MS

Overload protection		yes	
Detection zone			
Sensing range	[mm]	4	
Real sensing range Sr	[mm]	4 ± 10 %	
Operating distance	[mm]	0...3.25	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	3...15	
Switch point drift	[X01]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		threaded type	
Mounting		non-flush mountable	
Dimensions	[mm]	M12 x 1	
Thread designation		M12 x 1	
Materials		brass nickel-plated; CO-PC	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Аксессуары			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	

IF5266



Inductive sensor

IFB3004-BPKG/MS

Electrical connection

Cable: 2 m, PVC; 3 x 0.34 mm²

Connection



BN =	Core colours :
BU =	brown
BK =	blue
	black