




## Inductive sensor

IFB3007-APKG/US-104



### Product characteristics

|                    |                  |
|--------------------|------------------|
| Electrical design  | PNP              |
| Output function    | normally closed  |
| Sensing range [mm] | 7                |
| Housing            | threaded type    |
| Dimensions [mm]    | M12 x 1 / L = 50 |

### Application

|                 |                                               |
|-----------------|-----------------------------------------------|
| Special feature | Gold-plated contacts; Increased sensing range |
| Application     | Industrial applications / factory automation  |

### Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...30 DC |
| Current consumption [mA]    | < 10       |
| Protection class            | II         |
| Reverse polarity protection | yes        |

### Outputs

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Electrical design                                    | PNP             |
| Output function                                      | normally closed |
| Max. voltage drop switching output DC [V]            | 2.5             |
| Permanent current rating of switching output DC [mA] | 100             |
| Switching frequency DC [Hz]                          | 700             |
| Short-circuit protection                             | yes             |
| Overload protection                                  | yes             |

### Detection zone

|                            |          |
|----------------------------|----------|
| Sensing range [mm]         | 7        |
| Real sensing range Sr [mm] | 7 ± 10 % |
| Operating distance [mm]    | 0...5.67 |
| Increased sensing range    | yes      |

### Accuracy / deviations

|                   |                                                                             |
|-------------------|-----------------------------------------------------------------------------|
| Correction factor | steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3 |
| Hysteresis [X01]  | 3...15                                                                      |



## Inductive sensor

IFB3007-APKG/US-104

|                    |       |          |
|--------------------|-------|----------|
| Switch point drift | [X01] | -10...10 |
|--------------------|-------|----------|

## Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...70 |
| Protection          |      | IP 67    |

## Tests / approvals

|                            |                           |                   |
|----------------------------|---------------------------|-------------------|
| EMC                        | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD |
|                            | EN 61000-4-3 HF radiated  | 10 V/m            |
|                            | EN 61000-4-4 Burst        | 2 kV              |
|                            | EN 61000-4-6 HF conducted | 10 V              |
|                            | EN 55011                  | class B           |
| MTTF                       | [ANN]                     | 1134              |
| Embedded software included |                           | no                |
| UL approval                | Ta                        | 0...40 °C         |
|                            | Enclosure type            | Type 1            |
|                            | подача напруги            | Hazardous voltage |
|                            | UL Approval no.           | A003              |
|                            | File number UL            | E174191           |

## Mechanical data

|                    |      |                                                                                                                        |
|--------------------|------|------------------------------------------------------------------------------------------------------------------------|
| Weight             | [g]  | 25.1                                                                                                                   |
| Housing            |      | threaded type                                                                                                          |
| Mounting           |      | non-flush mountable                                                                                                    |
| Dimensions         | [mm] | M12 x 1 / L = 50                                                                                                       |
| Thread designation |      | M12 x 1                                                                                                                |
| Materials          |      | housing: brass white bronze coated; sensing face: PBT orange;<br>LED window: PEI; lock nuts: brass white bronze coated |

## Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 4 x LED, yellow |
|---------|------------------|-----------------|

## Аксессуары

|                |              |
|----------------|--------------|
| Items supplied | lock nuts: 2 |
|----------------|--------------|

## Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

## Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated





## Inductive sensor

IFB3007-APKG/US-104

### Connection

