

IG0319




Inductive sensor

IGA2008UARLA/SC/SL/LS-100AK

Article no longer available - archive entry

Alternative articles: IG0334
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics	
Output function	normally open
Sensing range [mm]	8
Housing	threaded type
Dimensions [mm]	M18 x 1
Application	
Special feature	Magnetic-field immune
Magnetic-field immune	yes
Electrical data	
Frequency AC [Hz]	47...63
Operating voltage [V]	20...140 AC/DC
Protection class	I
Reverse polarity protection	no
Outputs	
Output function	normally open
Max. voltage drop switching output DC [V]	5.5
Max. voltage drop switching output AC [V]	5.5
Minimum load current [mA]	5.5



Inductive sensor

IGA2008UARLA/SC/SL/LS-100AK

Max. leakage current	[mA]	1.7 (140 V AC/DC)
Permanent current rating of switching output AC	[mA]	300
Permanent current rating of switching output DC	[mA]	420
Short-time current rating of switching output	[mA]	420; (/ 300 AC (20ms / 0,5Hz))
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		latching (restart interlock after short circuit)
Overload protection		no

Detection zone

Sensing range	[mm]	8
Real sensing range Sr	[mm]	8 ± 10 %
Operating distance	[mm]	0...6.5

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[X01]	3...15
Switch point drift	[X01]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1
Thread designation		M18 x 1
Materials		brass; PES; PTFE coated

Displays / operating elements

Display	switching status	1 x LED, red
	operation	1 x LED, green
	short circuit	1 x LED, green/red alternately flashing

Аксессуары

Items supplied		lock nuts: 2
----------------	--	--------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

IG0319



Inductive sensor

IGA2008UARLA/SC/SL/LS-100AK

Electrical connection - plug

Connector: 1 x 1/2"; coding: C

