

# IG5381



## Inductive sensor

IGA3008-ANKG



### Product characteristics

|                    |                  |
|--------------------|------------------|
| Electrical design  | NPN              |
| Output function    | normally open    |
| Sensing range [mm] | 8                |
| Housing            | threaded type    |
| Dimensions [mm]    | M18 x 1 / L = 80 |

### Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...36 DC |
| Current consumption [mA]    | 15; (24 V) |
| Protection class            | II         |
| Reverse polarity protection | yes        |

### Outputs

|                                                      |               |
|------------------------------------------------------|---------------|
| Electrical design                                    | NPN           |
| Output function                                      | normally open |
| Max. voltage drop switching output DC [V]            | 2.5           |
| Permanent current rating of switching output DC [mA] | 250           |
| Switching frequency DC [Hz]                          | 300           |
| Short-circuit protection                             | yes           |
| Type of short-circuit protection                     | pulsed        |
| Overload protection                                  | yes           |

### Detection zone

|                            |          |
|----------------------------|----------|
| Sensing range [mm]         | 8        |
| Real sensing range Sr [mm] | 8 ± 10 % |
| Operating distance [mm]    | 0...6.5  |

### Accuracy / deviations

|                          |                                                                             |
|--------------------------|-----------------------------------------------------------------------------|
| Correction factor        | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |
| Hysteresis [X01]         | 1...15                                                                      |
| Switch point drift [X01] | -10...10                                                                    |

# IG5381



## Inductive sensor

IGA3008-ANKG

### Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...80 |
| Protection          |      | IP 67    |

### Tests / approvals

|      |              |         |
|------|--------------|---------|
| EMC  | EN 60947-5-2 |         |
|      | EN 55011     | class B |
| MTTF | [ANN]        | 1754    |

### Mechanical data

|                    |      |                               |
|--------------------|------|-------------------------------|
| Weight             | [g]  | 160.1                         |
| Housing            |      | threaded type                 |
| Mounting           |      | non-flush mountable           |
| Dimensions         | [mm] | M18 x 1 / L = 80              |
| Thread designation |      | M18 x 1                       |
| Materials          |      | brass white bronze coated; PC |

### Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 1 x LED, yellow |
|---------|------------------|-----------------|

### Аксессуары

|                |              |
|----------------|--------------|
| Items supplied | lock nuts: 2 |
|----------------|--------------|


### Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

### Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm²

### Connection



|      |                |
|------|----------------|
| BN = | Core colours : |
| BU = | brown          |
| BK = | blue           |
|      | black          |