

## Inductive sensor

IG-3005-APOG

Article no longer available - archive entry

Alternative articles: IG5400

When selecting an alternative article and accessories please note that technical data may differ!



### Product characteristics

|                    |                  |
|--------------------|------------------|
| Electrical design  | PNP              |
| Output function    | normally closed  |
| Sensing range [mm] | 5                |
| Housing            | threaded type    |
| Dimensions [mm]    | M18 x 1 / L = 80 |

### Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...55 DC |
| Current consumption [mA]    | 15; (24 V) |
| Protection class            | II         |
| Reverse polarity protection | no         |

### Outputs

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Electrical design                                    | PNP             |
| Output function                                      | normally closed |
| Max. voltage drop switching output DC [V]            | 1               |
| Permanent current rating of switching output DC [mA] | 400             |
| Switching frequency DC [Hz]                          | 200             |
| Short-circuit protection                             | no              |
| Overload protection                                  | no              |

### Detection zone

|                               |               |
|-------------------------------|---------------|
| Sensing range [mm]            | 5             |
| Real sensing range $S_r$ [mm] | $5 \pm 10 \%$ |
| Operating distance [mm]       | 0...4.05      |

### Accuracy / deviations

|                          |                                                                             |
|--------------------------|-----------------------------------------------------------------------------|
| Correction factor        | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3 |
| Hysteresis [X01]         | 1...15                                                                      |
| Switch point drift [X01] | -10...10                                                                    |

# IG5002



## Inductive sensor

IG-3005-APOG

### Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...80 |
| Protection          |      | IP 67    |

### Mechanical data

|                    |      |                  |
|--------------------|------|------------------|
| Housing            |      | threaded type    |
| Mounting           |      | flush mountable  |
| Dimensions         | [mm] | M18 x 1 / L = 80 |
| Thread designation |      | M18 x 1          |
| Materials          |      | PBT              |

### Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 1 x LED, yellow |
|---------|------------------|-----------------|

### Аксессуары

|                |  |              |
|----------------|--|--------------|
| Items supplied |  | lock nuts: 2 |
|----------------|--|--------------|


### Remarks

|               |  |        |
|---------------|--|--------|
| Pack quantity |  | 1 pcs. |
|---------------|--|--------|

### Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm<sup>2</sup>

### Connection



Core colours :  
BK = black  
BN = brown  
BU = blue