

# IG5254




## Inductive sensor

IGB3005-BPKG/MS

Article no longer available - archive entry

Alternative articles: IG5698

When selecting an alternative article and accessories please note that technical data may differ!



### Product characteristics

|                    |               |
|--------------------|---------------|
| Electrical design  | PNP           |
| Output function    | normally open |
| Sensing range [mm] | 5             |
| Housing            | threaded type |
| Dimensions [mm]    | M18 x 1       |

### Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 18...36 DC |
| Current consumption [mA]    | 15; (24 V) |
| Protection class            | II         |
| Reverse polarity protection | yes        |

### Outputs

|                                                      |                       |
|------------------------------------------------------|-----------------------|
| Electrical design                                    | PNP                   |
| Output function                                      | normally open         |
| Max. voltage drop switching output DC [V]            | 2.5                   |
| Permanent current rating of switching output DC [mA] | 125; (150 (...50 °C)) |
| Switching frequency DC [Hz]                          | 500                   |
| Short-circuit protection                             | yes                   |
| Type of short-circuit protection                     | pulsed                |
| Overload protection                                  | yes                   |

### Detection zone

|                            |          |
|----------------------------|----------|
| Sensing range [mm]         | 5        |
| Real sensing range Sr [mm] | 5 ± 10 % |
| Operating distance [mm]    | 0...4.05 |

### Accuracy / deviations

|                   |                                                                             |
|-------------------|-----------------------------------------------------------------------------|
| Correction factor | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |
|-------------------|-----------------------------------------------------------------------------|

# IG5254



## Inductive sensor

IGB3005-BPKG/MS

|                    |       |          |
|--------------------|-------|----------|
| Hysteresis         | [X01] | 1...15   |
| Switch point drift | [X01] | -10...10 |

### Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...80 |
| Protection          |      | IP 67    |

### Tests / approvals

|     |              |         |
|-----|--------------|---------|
| EMC | EN 60947-5-2 |         |
|     | EN 55011     | class B |

### Mechanical data

|                    |      |                          |
|--------------------|------|--------------------------|
| Housing            |      | threaded type            |
| Mounting           |      | flush mountable          |
| Dimensions         | [mm] | M18 x 1                  |
| Thread designation |      | M18 x 1                  |
| Materials          |      | brass nickel-plated; PBT |

### Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 1 x LED, yellow |
|---------|------------------|-----------------|

### Аксессуары

|                |  |              |
|----------------|--|--------------|
| Items supplied |  | lock nuts: 2 |
|----------------|--|--------------|


### Remarks

|               |  |        |
|---------------|--|--------|
| Pack quantity |  | 1 pcs. |
|---------------|--|--------|

### Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm<sup>2</sup>

### Connection



|      |                |
|------|----------------|
|      | Core colours : |
| BN = | brown          |
| BU = | blue           |
| BK = | black          |