

## Inductive sensor


II-3015-BPKG

RT

Article no longer available - archive entry

Alternative articles: II5300

When selecting an alternative article and accessories please note that technical data may differ!



## Product characteristics

|                    |                    |
|--------------------|--------------------|
| Electrical design  | PNP                |
| Output function    | normally open      |
| Sensing range [mm] | 15                 |
| Housing            | threaded type      |
| Dimensions [mm]    | M30 x 1.5 / L = 81 |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...36 DC |
| Current consumption [mA]    | < 5        |
| Protection class            | II         |
| Reverse polarity protection | yes        |

## Outputs

|                                                      |               |
|------------------------------------------------------|---------------|
| Electrical design                                    | PNP           |
| Output function                                      | normally open |
| Max. voltage drop switching output DC [V]            | 2.5           |
| Permanent current rating of switching output DC [mA] | 250           |
| Switching frequency DC [Hz]                          | 250           |
| Short-circuit protection                             | yes           |
| Type of short-circuit protection                     | pulsed        |
| Overload protection                                  | yes           |

## Detection zone

|                               |                |
|-------------------------------|----------------|
| Sensing range [mm]            | 15             |
| Real sensing range $S_r$ [mm] | $15 \pm 10 \%$ |
| Operating distance [mm]       | 0...12.1       |



## Inductive sensor

II-3015-BPKG

RT

## Accuracy / deviations

|                    |       |                                                                             |
|--------------------|-------|-----------------------------------------------------------------------------|
| Correction factor  |       | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |
| Hysteresis         | [X01] | 1...15                                                                      |
| Switch point drift | [X01] | -10...10                                                                    |

## Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...80 |
| Protection          |      | IP 67    |

## Tests / approvals

|     |              |         |
|-----|--------------|---------|
| EMC | EN 60947-5-2 |         |
|     | EN 55011     | class B |

## Mechanical data

|                    |      |                     |
|--------------------|------|---------------------|
| Housing            |      | threaded type       |
| Mounting           |      | non-flush mountable |
| Dimensions         | [mm] | M30 x 1.5 / L = 81  |
| Thread designation |      | M30 x 1.5           |
| Materials          |      | PBT                 |

## Displays / operating elements

|         |                  |              |
|---------|------------------|--------------|
| Display | switching status | 1 x LED, red |
|---------|------------------|--------------|

## Аксессуары

|                |  |              |
|----------------|--|--------------|
| Items supplied |  | lock nuts: 2 |
|----------------|--|--------------|


## Remarks

|               |  |        |
|---------------|--|--------|
| Pack quantity |  | 1 pcs. |
|---------------|--|--------|

## Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm<sup>2</sup>

## Connection



Core colours :  
 BK = black  
 BN = brown  
 BU = blue