


## Inductive sensor

IIA2015-ABOW/V4A

Article no longer available - archive entry

Alternative articles: II0062

When selecting an alternative article and accessories please note that technical data may differ!



## Product characteristics

|                 |      |               |
|-----------------|------|---------------|
| Output function |      | normally open |
| Sensing range   | [mm] | 15            |
| Housing         |      | threaded type |
| Dimensions      | [mm] | M30 x 1.5     |

## Electrical data

|                             |      |             |
|-----------------------------|------|-------------|
| Frequency AC                | [Hz] | 47...63     |
| Operating voltage           | [V]  | 20...250 AC |
| Protection class            |      | II          |
| Reverse polarity protection |      | no          |

## Outputs

|                                                 |      |                        |
|-------------------------------------------------|------|------------------------|
| Output function                                 |      | normally open          |
| Max. voltage drop switching output AC           | [V]  | 5.5                    |
| Minimum load current                            | [mA] | 5                      |
| Max. leakage current                            | [mA] | 2.5                    |
| Permanent current rating of switching output AC | [mA] | 300; (500 (...50 °C))  |
| Short-time current rating of switching output   | [mA] | 2200; (20 ms / 0,5 Hz) |
| Switching frequency AC                          | [Hz] | 20                     |
| Short-circuit protection                        |      | no                     |
| Overload protection                             |      | no                     |



## Inductive sensor

IIA2015-ABOW/V4A

| Detection zone                           |                  |                                                                             |
|------------------------------------------|------------------|-----------------------------------------------------------------------------|
| Sensing range                            | [mm]             | 15                                                                          |
| Real sensing range Sr                    | [mm]             | 15 ± 10 %                                                                   |
| Operating distance                       | [mm]             | 0...12.1                                                                    |
| Accuracy / deviations                    |                  |                                                                             |
| Correction factor                        |                  | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |
| Hysteresis                               | [X01]            | 1...15                                                                      |
| Switch point drift                       | [X01]            | -10...10                                                                    |
| Operating conditions                     |                  |                                                                             |
| Ambient temperature                      | [°C]             | -25...80                                                                    |
| Protection                               |                  | IP 67                                                                       |
| Mechanical data                          |                  |                                                                             |
| Housing                                  |                  | threaded type                                                               |
| Mounting                                 |                  | non-flush mountable                                                         |
| Dimensions                               | [mm]             | M30 x 1.5                                                                   |
| Thread designation                       |                  | M30 x 1.5                                                                   |
| Materials                                |                  | stainless steel (1.4571/316Ti ); PBT                                        |
| Displays / operating elements            |                  |                                                                             |
| Display                                  | switching status | 1 x LED, yellow                                                             |
| Аксессуары                               |                  |                                                                             |
| Items supplied                           |                  | lock nuts: 2                                                                |
| Remarks                                  |                  |                                                                             |
| Pack quantity                            |                  | 1 pcs.                                                                      |
| Electrical connection                    |                  |                                                                             |
| Cable: 2 m, PVC; 2 x 0.5 mm <sup>2</sup> |                  |                                                                             |
| Connection                               |                  |                                                                             |



BN = Core colours :  
brown  
BU = blue