


Inductive sensor

IIB3015-BNOG/US-100-DNO

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5

Electrical data

Operating voltage [V]	18...36 DC
Current consumption [mA]	15; (24 V)
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	250
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	15
--------------------	----

I15458



Inductive sensor

IIB3015-BNOG/US-100-DNO

Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 65

Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Materials		brass nickel-plated; PBT

Displays / operating elements		
Display	switching status	1 x LED, yellow

Аксессуары		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection

