


IIR205



Inductive full-metal sensor

IIB2012BARKG/AM/SC/5,0M/2LED



Product characteristics	
Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	12
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 40
Application	
Special feature	Increased sensing range; Full-metal housing; Optical setting aid; anti-spatter
Application	Use in welding applications
Pressure rating [bar]	10
Note on pressure rating	sensing face
Electrical data	
Operating voltage [V]	10...30 DC
Protection class	III
Reverse polarity protection	yes
Outputs	
Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	3.2
Minimum load current [mA]	2
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	25

IIR205



Inductive full-metal sensor

IIB2012BARKG/AM/SC/5,0M/2LED

Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	12
Operating distance	[mm]	0...9.72
Increased sensing range		yes
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.7 / aluminium: 0.5 / copper: 0.1
Hysteresis	[X01]	1...20
Operating conditions		
Ambient temperature	[°C]	-40...85
Protection		IP 65; IP 66; IP 67; IP 68; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011 emission	class B
Impact resistance		1 J
MTTF	[ANN]	959
UL approval	Ta	0...40 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	UL Approval no.	A042
	File number UL	E174191
Mechanical data		
Weight	[g]	299.5
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 40
Thread designation		M30 x 1.5
Materials		housing: stainless steel (316L/1.4404) anti-spatter; sensing face: stainless steel (316L/1.4404) anti-spatter; cable plug: PEI; lock nuts: stainless steel (316L/1.4404) anti-spatter
Tightening torque	[Nm]	60
Full-metal housing		yes
Displays / operating elements		
Display	switching status	1 x LED, green
	setting aid	1 x LED, red
Optical setting aid		yes
Аксессуары		
Items supplied		lock nuts: 2

IIR205



Inductive full-metal sensor

IIB2012BARKG/AM/SC/5,0M/2LED


Remarks

Pack quantity 1 pcs.

Electrical connection

Cable: 5 m, PVC; 2 x 0.5 mm²

Connection



BN = Core colours : brown
BU = blue

Diagrams and graphs

Installation

