




Inductive sensor

IIB2015BBRKG/2M/PUR/UP



1 LED yellow



Product characteristics		
Electrical design		PNP/NPN
Output function		normally closed
Sensing range	[mm]	15
Housing		threaded type
Dimensions	[mm]	M30 x 1.5 / L = 45
Application		
Special feature		Drag chain suitability; Increased sensing range
Application		Industrial applications / factory automation
Electrical data		
Operating voltage	[V]	10...30 DC; ("supply limited voltage / current" to UL)
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally closed
Max. voltage drop switching output DC	[V]	5
Minimum load current	[mA]	2
Max. leakage current	[mA]	0.6
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Overload protection		yes
Detection zone		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.15



Inductive sensor

IIB2015BBRKG/2M/PUR/UP

Increased sensing range		yes	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis [X01]		3...15	
Switch point drift [X01]		-10...10	
Operating conditions			
Ambient temperature [°C]		-40...85	
Protection		IP 65; IP 66; IP 67; IP 68; IP 69K	
Tests / approvals			
EMC	EN 61000-4-2 ESD		4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated		10 V/m
	EN 61000-4-4 Burst		2 kV
	EN 61000-4-6 HF conducted		10 V
	EN 55011		class B
Vibration resistance	EN 60068-2-6 Fc		20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes
Shock resistance	EN 60068-2-27 Ea		100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance	EN 60068-2-27		40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes
Fast temperature change	EN 60068-2-14 Na		TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles
Salt spray test	EN 60068-2-52 Kb		severity level 5 (4 test cycles)
MTTF [ANN]	899		
Embedded software included	yes		
UL approval	Ta		-25...75 °C
	Enclosure type		Type 1
	подача напруги		Limited Voltage/Current
	UL Approval no.		A007
	File number UL		E174191
Mechanical data			
Weight [g]	150.2		
Housing	threaded type		
Mounting	flush mountable		
Dimensions [mm]	M30 x 1.5 / L = 45		
Thread designation	M30 x 1.5		
Materials	brass white bronze coated; sensing face: PBT orange; LED window: PEI; lock nuts: brass white bronze coated		
Tightening torque [Nm]	see operating instructions		
Drag chain suitability	yes		
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter	
	bending cycles	> 5 Mio.	
Displays / operating elements			
Display	switching status	1 x LED, yellow	
Аксессуары			
Items supplied	lock nuts: 2		
	Tooth lock washer: 1, stainless steel		

IIS714



Inductive sensor

IIB2015BBRKG/2M/PUR/UP

Remarks


Pack quantity

1 pcs.

Electrical connection

Cable: 2 m, PUR; 2 x 0.34 mm²

Connection



BK =

Core colours :
black