

IK7001




Inductive sensor

SIK-3020-BPKG

Article no longer available - archive entry

Alternative articles: IIT207
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	20
Housing		threaded type
Dimensions	[mm]	M38 x 1.5
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	60
Short-circuit protection		yes

IK7001



Inductive sensor

SIK-3020-BPKG

Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M38 x 1.5
Thread designation	M38 x 1.5	
Materials	brass white bronze coated; PBT	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	

IK7001




Inductive sensor

SIK-3020-BPKG

Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm²

Connection



BN =	Core colours :
BU =	brown
BK =	blue
	black