




Inductive AS-Interface sensor

IMC2015-ASI /US-100

Article no longer available - archive entry

Alternative articles: IM5118
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		AS-i
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 66
Application		
Special feature		Gold-plated contacts
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 30
Reverse polarity protection		yes
Outputs		
Electrical design		AS-i
Short-circuit protection		yes



Inductive AS-Interface sensor

IMC2015-ASI /US-100

Type of short-circuit protection	pulsed				
Overload protection	yes				
Detection zone					
Sensing range	[mm]	15			
Operating conditions					
Ambient temperature	[°C]	-25...70			
Protection	IP 67				
Tests / approvals					
EMC	EN 60947-5-2				
	EN 55011		class B		
AS-i classification					
AS-i I/O configuration	[hex]	1			
AS-i ID code	[hex]	1			
Assignment of the data bits	Type	input	input	input	Output
	Designation	switching signal	safe zone	readiness for operation	test
	status = 0	target outside the active zone	target within the uncertain zone	faulty device or target collided with the sensor	not used
	status = 1	target within the active zone	target within the certain zone	unit ready for operation	not used
Mechanical data					
Housing	rectangular				
Mounting	flush mountable				
Dimensions	[mm]	40 x 40 x 66			
Materials	housing: PBT; sensing face: PPE; clamp: PPS				
Displays / operating elements					
Display	switching status		1 x LED, yellow		
	unsafe zone		1 x LED, red sensor coil wire break, sensor coil short circuit Sr: 0...10 % (< 10 Hz) Sn: 80...115 % (< 10 Hz)		
Аксессуары					
Items supplied	Mounting bracket: 1				
	Allen key: 1				
Remarks					
Remarks	5 positions of the active zone possible				
	Assured range: approx. 10...80 % of Sn				
Pack quantity	1 pcs.				

IM5055



Inductive AS-Interface sensor

IMC2015-ASI /US-100

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

