




Inductive sensor

IMC4020BCPKG/US-100-DPA

Article no longer available - archive entry

Alternative articles: IM5123

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	20
Housing	rectangular
Dimensions [mm]	40 x 40 x 66

Application

Special feature	Gold-plated contacts
-----------------	----------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	20; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
-------------------	-----



Inductive sensor

IMC4020BCPKG/US-100-DPA

Output function		complementary
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone		
Sensing range	[mm]	20
Real sensing range S_r	[mm]	$20 \pm 10 \%$
Operating distance	[mm]	0...16.2

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.8 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	3...15
Switch point drift	[X01]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	40 x 40 x 66
Materials		housing: PPE; sensing face: PPE; end cap: PPS; clamp: PPS

Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Аксессуары		
Items supplied		Mounting bracket: 1
		Allen key: 1

Remarks		
Pack quantity		1 pcs.

IM5068



Inductive sensor

IMC4020BCPKG/US-100-DPA

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

