


IM5069



Inductive sensor

IMC3015ZBPKG/US-100-DPS

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 66
Application		
Special feature		Gold-plated contacts
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open



Inductive sensor

IMC3015ZBPKG/US-100-DPS

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	300
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10

Operating conditions		
Ambient temperature	[°C]	0...100
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	

Mechanical data		
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	40 x 40 x 66
Materials		housing: PBT; sensing face: PPE; clamp: PPS

Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Аксессуары		
Items supplied	Mounting bracket: 1	
	Allen key: 1	

Remarks		
Remarks		5 positions of the active zone possible
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



IM5069



Inductive sensor

IMC3015ZBPKG/US-100-DPS

Connection

