


Inductive sensor

IIA4015LCPKG/V4A/TS-600-APA

Article no longer available - archive entry

Alternative articles: II5760

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5

Electrical data

Operating voltage [V]	18...30 DC
Current consumption [mA]	7; (24 V)
Reverse polarity protection	no


Outputs

Electrical design	PNP
Output function	complementary
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	50
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes



Inductive sensor

IIA4015LCPKG/V4A/TS-600-APA

Detection zone		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.54 / aluminium: 0.5 / copper: 0.46
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 65
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Materials		stainless steel (1.4571/316Ti); PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x Ø 28 mm; coding: A		
		

Inductive sensor

IIA4015LCPKG/V4A/TS-600-APA

Connection

