




Inductive sensor

IIB3010-BPKG/TS-600-APS

Article no longer available - archive entry

Alternative articles: II5766
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics	
Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Housing	threaded type
Dimensions [mm]	M30 x 1.5
Electrical data	
Operating voltage [V]	18...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes
Outputs	
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	125; (150 (...50 °C))
Switching frequency DC [Hz]	300
Short-circuit protection	yes



Inductive sensor

IIB3010-BPKG/TS-600-APS

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone	
Sensing range [mm]	10
Real sensing range S_r [mm]	$10 \pm 10\%$
Operating distance [mm]	0...0.8

Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis [X01]	3...15
Switch point drift [X01]	-10...10

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 65

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data	
Housing	threaded type
Mounting	flush mountable
Dimensions [mm]	M30 x 1.5
Thread designation	M30 x 1.5
Materials	brass nickel-plated; PBT

Displays / operating elements		
Display	switching status	1 x LED, yellow

Аксессуары	
Items supplied	lock nuts: 2

Remarks	
Remarks	Note:
	Pin connection does not conform to DIN EN 50044.
	The protective earth in the connector must not be used.
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x Ø 28 mm; coding: A



II5227



Inductive sensor

IIB3010-BPKG/TS-600-APS

Connection

