


Inductive sensor

IVE4020ZCPKG/20M



- 1 LED green
2 LED yellow



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	20
Housing	rectangular
Dimensions [mm]	40 x 40 x 118

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	20; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	complementary
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	300
Short-circuit protection	yes

IV5059



Inductive sensor

IVE4020ZCPKG/20M

Type of short-circuit protection	pulsed	
Overload protection	yes	
Detection zone		
Sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.3	
Hysteresis	[X01]	1...10
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...100
Protection	IP 68; IP 69K	
Tests / approvals		
EMC	EN 61000-4-2 ESD	8 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	15 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	10 g (10...2000 Hz) / 10 cycles
Shock resistance	EN 60068-2-27 Ea	30 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance	EN 60068-2-27	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes
Fast temperature change	EN 60068-2-14 Na	TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles
MTTF	[ANN]	652.2
UL approval	Ta	0...40 °C
	Enclosure type	Type 1
	File number UL	E174191
Mechanical data		
Weight	[g]	1438
Housing	rectangular	
Mounting	flush mountable	
Dimensions	[mm]	40 x 40 x 118
Materials	PA 6.6; diecast zinc epoxy coated; sensing face: PA 6.6; LED window: PA; гвинти: stainless steel stainless steel (1.4305 / 303)	
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Remarks		
Remarks	5 positions of the active zone possible	
Pack quantity	1 pcs.	

IV5059




Inductive sensor

IVE4020ZCPKG/20M

Electrical connection

Cable: 20 m, PVC; 4 x 0.50 mm²

Connection



BK =	Core colours :
BN =	black
BU =	brown
WH =	blue
	white