

IY5031




Inductive sensor

IYB20,8-BROG

Article no longer available - archive entry

Alternative articles: IY5033

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP/NPN
Output function	normally closed
Sensing range [mm]	0.8
Housing	threaded type
Dimensions [mm]	M5 x 0.5 / L = 30

Electrical data

Operating voltage [V]	10...36 DC
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	0.8
Real sensing range S_r [mm]	$0.8 \pm 10\%$
Operating distance [mm]	0...0.65

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10

IY5031



Inductive sensor

IYB20,8-BROG

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M5 x 0.5 / L = 30
Thread designation		M5 x 0.5
Materials		stainless steel (1.4305 / 303); POM

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied		lock nuts: 2
----------------	--	--------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 2 m, PVC; 2 x 0.14 mm²

Connection

