




Inductive sensor

IYB31,5-BPKG/AS-514-TPS



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1.5
Housing	threaded type
Dimensions [mm]	M5 x 0.5 / L = 41

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	10; (24 V)
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	3
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	1800
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	1.5
Real sensing range S_r [mm]	$1.5 \pm 10\%$
Operating distance [mm]	0...1.2

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [X01]	< 15
Switch point drift [X01]	-10...10

Operating conditions

Ambient temperature [°C]	-25...70
--------------------------	----------

IY5048



Inductive sensor

IYB31,5-BPKG/AS-514-TPS

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[ANN]	835
UL approval	Ta	0...40 °C
	подача напруги	Class 2
	File number UL	E174191

Mechanical data

Weight	[g]	15.8
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M5 x 0.5 / L = 41
Thread designation		M5 x 0.5
Materials		housing: stainless steel; sensing face: POM

Displays / operating elements

Display	switching status	4 x 90° LED, red
---------	------------------	------------------

Аксессуары

Items supplied	lock nuts: 2
----------------	--------------

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



Connection




Inductive sensor

IYB31,5-BPKG/AS-514-TPS

Diagrams and graphs

Installation



If S_r varies by $< 10\%$ the following free space must be maintained ferromagnetic materials $X > 1.5\text{ mm}$ other metals $X > 3.0\text{ mm}$