

IM5058




Inductive sensor

IMC3015UBPKG/SC/US-100-DPS

Article no longer available - archive entry

Alternative articles: IM5119
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 66
Application		
Special feature		Gold-plated contacts; Magnetic-field immune; anti-spatter
Magnetic-field immune		yes
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes



Inductive sensor

IMC3015UBPKG/SC/US-100-DPS

Outputs		
Electrical design	PNP	
Output function	normally open	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	250	
Switching frequency DC [Hz]	300	
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Detection zone		
Sensing range [mm]	15	
Real sensing range Sr [mm]	15 ± 10 %	
Operating distance [mm]	0...12.1	
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis [X01]	1...15	
Switch point drift [X01]	-10...10	
Operating conditions		
Ambient temperature [°C]	-25...70	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	rectangular	
Mounting	flush mountable	
Dimensions [mm]	40 x 40 x 66	
Materials	housing: PBT; sensing face: PEI anti-spatter; clamp: PPS	
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Аксессуары		
Items supplied	Mounting bracket: 1	
	Allen key: 1	
Remarks		
Remarks	5 positions of the active zone possible	
Pack quantity	1 pcs.	

IM5058



Inductive sensor

IMC3015UBPKG/SC/US-100-DPS

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

