

IM5089




Inductive sensor

IMC4035-CPKG/SC/US-100-DPA

Article no longer available - archive entry

Alternative articles: IM5125 or IM5126

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	35
Housing		rectangular
Dimensions	[mm]	40 x 40 x 62
Application		
Special feature		Gold-plated contacts; anti-spatter
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP



Inductive sensor

IMC4035-CPKG/SC/US-100-DPA

Output function		complementary
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone		
Sensing range	[mm]	35
Real sensing range S_r	[mm]	$35 \pm 10 \%$
Operating distance	[mm]	0...28.3

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	

Mechanical data		
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 40 x 62
Materials		housing: PPE; sensing face: PEI anti-spatter; end cap: diecast zinc; clamp: diecast zinc

Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Аксессуары		
Items supplied		Mounting bracket: 1
		Allen key: 1

Remarks		
Remarks		5 positions of the active zone possible
Pack quantity		1 pcs.

IM5089



Inductive sensor

IMC4035-CPKG/SC/US-100-DPA

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

