


Capacitive sensor

KB-3020-BNKG/NI

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	3...20
Housing	cylindrical
Dimensions [mm]	Ø 34 / L = 81

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	13; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	40
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	3...20
Sensing range adjustable	yes
Factory setting sensing range [mm]	20
Real sensing range S_r [mm]	$20 \pm 10 \%$
Operating distance [mm]	0...16.2

Accuracy / deviations

Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
-------------------	--



Capacitive sensor

KB-3020-BNKG/NI

Hysteresis	[X01]	1...15
Switch point drift	[X01]	-15...15

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 65
Increased immunity		yes; (increased immunity to conducted radio frequency interference)

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 34 / L = 81
Materials		PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied	кріпильні хомути: 1
	screwdriver: 1

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm²

Connection



Core colours :

BN = brown

BU = blue

BK = black