




Inductive sensor

IN-3004-BNOG

Article no longer available - archive entry



- 1 mounting hole
- 2 threaded bush M3 Depth 5.8 mm



Product characteristics		
Electrical design		NPN
Output function		normally closed
Sensing range	[mm]	4
Housing		rectangular
Dimensions	[mm]	40 x 12 x 26
Electrical data		
Operating voltage	[V]	10...55 DC
Current consumption	[mA]	15; (24 V)
Reverse polarity protection		no
Outputs		
Electrical design		NPN
Output function		normally closed
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	250
Short-circuit protection		no
Overload protection		no
Detection zone		
Sensing range	[mm]	4
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2

IN5007



Inductive sensor

IN-3004-BNOG

Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 12 x 26
Materials		PBT

Mounting hole		
Tightening torque	[Nm]	< 0.5

Threaded bush		
Tightening torque	[Nm]	< 1.2; (when brass insert in contact with counterpart)


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue