


KQ5005



Capacitive sensor

KQ-3073NAPKG



- 1 LED
- 2 Sensing face



Product characteristics		
Electrical design		PNP
Output function		normally closed
Sensing range	[mm]	7.3; (fixed: 7,3)
Housing		rectangular
Dimensions	[mm]	57 x 36 x 10
Application		
Application		level detection of demineralised water
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 17
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally closed
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	10
Short-circuit proof		yes
Overload protection		yes
Detection zone		
Sensing range	[mm]	7.3; (fixed: 7,3)
Accuracy / deviations		
Correction factor		glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-20...20

KQ5005



Capacitive sensor

KQ-3073NAPKG

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65; IP 67; IP 69K

Tests / approvals

EMC		EN 60947-5-2	
MTTF	[ANN]		771
UL approval		Ta	-25...80 °C
		Enclosure type	Type 1
		подача напруги	Class 2

Mechanical data

Weight	[g]	67.7
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	57 x 36 x 10
Materials		PBT; TPE-U; stainless steel

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied	mounting adapter: 1
----------------	---------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PUR; 3 x 0.14 mm²

Connection



BN	Core colours :
BK	brown
BU	black
	blue