




Inductive sensor

IOW2010-ARKG/UP/US-100 RT



1 snap-fit mounting



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	10
Housing		rectangular
Dimensions	[mm]	26 x 26 x 43
Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	2
Max. leakage current	[mA]	0.6
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	250
Short-circuit protection		yes
Type of short-circuit protection		pulsed



Inductive sensor

IOW2010-ARKG/UP/US-100 RT

Overload protection	yes	
Detection zone		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[ANN]	2577
Mechanical data		
Weight	[g]	45.78
Housing	rectangular	
Mounting	flush mountable	
Dimensions	[mm]	26 x 26 x 43
Materials	PA	
Displays / operating elements		
Display	switching status	1 x LED, red
Аксессуары		
Items supplied	head cap screw: 1 x M4 x 12	
Remarks		
Pack quantity	1 pcs.	
Electrical connection - plug		
Connector: 1 x M12; coding: A; Locking: rotatable		
		

IO5016



Inductive sensor

IOW2010-ARKG/UP/US-100 RT

Connection

