




Inductive sensor

IOW2010-ARKG/0,8M/US/UP RT



1 snap-fit mounting



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	10
Housing	rectangular
Dimensions [mm]	26 x 26 x 26

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	2
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	250
Short-circuit protection	yes
Type of short-circuit protection	pulsed



Inductive sensor

IOW2010-ARKG/0,8M/US/UP RT

Overload protection	yes
---------------------	-----

Detection zone

Sensing range	[mm]	10
Real sensing range S_r	[mm]	$10 \pm 10 \%$
Operating distance	[mm]	0...8.1

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[ANN]	2577

Mechanical data

Weight	[g]	72.5
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	26 x 26 x 26
Materials		PA

Displays / operating elements

Display	switching status	1 x LED, red
---------	------------------	--------------

Аксессуары

Items supplied	head cap screw: 1 x M4 x 12
----------------	-----------------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Cable: 0.8 m, PUR; 3 x 0.14 mm²

Connector: 1 x M12; coding: A



IO5017



Inductive sensor

IOW2010-ARKG/0,8M/US/UP RT

Connection

