

KT5050



Capacitive touch sensor

KTRSH-KGRBPKG/2M



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	Ø 96.9 / L = 11

Application

Operating principle	static
Application	reduced sensitivity

Electrical data

Operating voltage [V]	12...30 DC
Current consumption [mA]	30
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	500

Outputs

Electrical design	PNP
Output function	normally open
Permanent current rating of switching output DC [mA]	200
Short-circuit protection	yes
Overload protection	yes

Response times

Response time [ms]	35
--------------------	----

KT5050



Capacitive touch sensor

KTRSH-KGRBPKG/2M

Operating conditions

Ambient temperature	[°C]	-40...85
Protection		IP 65; IP 67; IP 69K; (on the front)

Mechanical data

Weight	[g]	142
Dimensions	[mm]	Ø 96.9 / L = 11
Materials		active face: PA Grilamid TR 90UV transparent; housing: PC/ABS black

Displays / operating elements

Display	switching status	8 x LED, red
	operation	8 x LED, green

Аксессуары

Accessories (optional)	surround in different colours
------------------------	-------------------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PUR

Connection



Core colours :
BK = black
BN = brown
BU = blue