

Inductive sensor

IOC2010-BRKG/0,15M/FRONT/POLAR

Article no longer available - archive entry



- 1 mounting holes M4 reinforced
2 Sensing face



Product characteristics

Electrical design	PNP/NPN
Output function	normally closed
Sensing range [mm]	10
Housing	rectangular
Dimensions [mm]	26 x 26 x 42

Electrical data

Operating voltage [V]	10...55 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.8
Minimum load current [mA]	2
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	250
Short-circuit protection	yes



Inductive sensor

IOC2010-BRKG/0,15M/FRONT/POLAR

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range	[mm]	10
Real sensing range S_r	[mm]	$10 \pm 10\%$
Operating distance	[mm]	0...8.1

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	26 x 26 x 42
Materials		PBT

Displays / operating elements

Display	switching status	1 x LED, red
---------	------------------	--------------



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 0.15 m, silicone; 2 x 1 mm²

Connection



Core colours :

BN = brown

BU = blue