




Inductive sensor

IVE4030-CPKG Elektronikteil

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	30
Housing		rectangular
Dimensions	[mm]	40 x 40 x 118
Electrical data		
Operating voltage	[V]	10...60 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		complementary
Max. voltage drop switching output DC	[V]	3
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	100

IV5038



Inductive sensor

IVE4030-CPKG Elektronikteil

Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	30
Real sensing range Sr	[mm]	30 ± 10 %
Operating distance	[mm]	0...24.3
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	rectangular	
Mounting	non-flush mountable	
Type of mounting	for mounting base; (E10228)	
Dimensions	[mm]	40 x 40 x 118
Materials	PBT	
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Remarks		
Remarks	5 positions of the active zone possible	
	Cable gland (E11270) to be ordered separately	
Pack quantity	1 pcs.	

IV5038



Inductive sensor

IVE4030-CPKG Elektronikteil

Electrical connection

Mounting base: ...2.5 mm²

Connection

