




Cylinder sensor for integrated profile cylinders

MKP3000-BPKG

Article no longer available - archive entry

Alternative articles: MK5115 + E11801
When selecting an alternative article and accessories please note that technical data may differ!



1 Sensing face



Product characteristics		
Electrical design		PNP
Output function		normally open
Dimensions	[mm]	41 x 30 x 27
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 10
Reverse polarity protection		yes
Max. power-on delay time	[ms]	2
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	300
Switching frequency DC	[Hz]	5000
Short-circuit protection		yes

MK5014



Cylinder sensor for integrated profile cylinders

MKP3000-BPKG

Type of short-circuit protection	pulsed	
Overload protection	yes	
Detection zone		
Response sensitivity	[mT]	3
Travel speed	[m/s]	< 5
Accuracy / deviations		
Hysteresis	[mm]	1
Repeatability	[mm]	0.1
Operating conditions		
Ambient temperature	[°C]	-25...75
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
Shock/vibration resistance	30 g (11 ms) / 10-55 Hz (1 mm)	
Mechanical data		
Sensing face	front	
Cylinder type	integrated profile cylinders	
Dimensions	[mm]	41 x 30 x 27
Materials	aluminium; plastics	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 2 m, PUR / PVC; 3 x 0.25 mm²		
Connection		



Core colours :
 BN = brown
 BU = blue
 BK = black