




Inductive sensor

IZ93001-BPKG/2M PVC



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1
Housing	cylindrical
Dimensions [mm]	Ø 3 / L = 27

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	12; (24 V)
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	no

Detection zone

Sensing range [mm]	1
Real sensing range Sr [mm]	1 ± 10 %
Operating distance [mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis [X01]	< 15	
Switch point drift [X01]	-10...10	

Operating conditions

Ambient temperature [°C]	0...70
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

IZ5048



Inductive sensor

IZ93001-BPKG/2M PVC

MTTF	[ANN]	735
UL approval	Ta	0...40 °C
	подача напруги	Class 2
	File number UL	E174191

Mechanical data

Weight	[g]	51
Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 3 / L = 27
Materials		housing: stainless steel; sensing face: POM

Displays / operating elements

Display	switching status	1 x LED, red
---------	------------------	--------------

Аксессуары

Items supplied	Mounting clamp:, E20107
----------------	-------------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.14 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue

IZ5048




Inductive sensor

IZ93001-BPKG/2M PVC

Diagrams and graphs

Installation



If S_r varies by $< 10\%$ the following free space must be maintained ferromagnetic materials $X > 1.5\text{ mm}$ other metals $X > 3.0\text{ mm}$