

NG500A



Inductive NAMUR sensor

IGB2012-N/US/1G/1D



Product characteristics

Electrical design	NAMUR
Output function	normally closed
Sensing range [mm]	12
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 51

Electrical data

Connection to switching amplifiers	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC [V]	8.2; (1kΩ)
Supply voltage DC [V]	7.5...30; (when used outside the hazardous area)
Current consumption [mA]	< 1; (disabled; conductive: > 2,1)
Protection class	II

Outputs

Electrical design	NAMUR
Output function	normally closed
Permanent current rating of switching output DC [mA]	30; (when used outside the hazardous area)
Switching frequency DC [Hz]	300

Detection zone

Sensing range [mm]	12
Real sensing range Sr [mm]	12 ± 10 %

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10

Operating conditions


Ambient temperature [°C]	-20...70
--------------------------	----------

NG500A



Inductive NAMUR sensor

IGB2012-N/US/1G/1D

Protection		IP 67	
Tests / approvals			
Approval		BVS 04 ATEX E 091 X; IECEx BVS 06.0003	
ATEX marking		 II 1G Ex ia IIC T6 Ga	
		 II 1D Ex ia IIIC T 90°C Da	
EMC		EN 60947-5-6	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)	
MTTF [ANN]		3387	
Safety classification			
Max. internal capacitance [nF]		200	
Max. internal inductance [μH]		85	
Mechanical data			
Weight [g]		90	
Housing		threaded type	
Mounting		non-flush mountable	
Dimensions [mm]		M18 x 1 / L = 51	
Thread designation		M18 x 1	
Materials		brass special coating; sensing face: PBT; LED window: PA	
Displays / operating elements			
Display		switching status	4 x 90° LED, yellow
Аксессуары			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection - plug			
Connector: 1 x M12; coding: A			
			

NG500A



Inductive NAMUR sensor

IGB2012-N/US/1G/1D

Connection



1 = connection to NAMUR amplifiers