

KG5026




Capacitive sensor

KGE2008-FRKG/US-100-IRF/0LED

Article no longer available - archive entry

Alternative articles: KG5001
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open / normally closed; (selectable)
Sensing range	[mm]	8
Housing		threaded type
Dimensions	[mm]	M18 x 1
Electrical data		
Operating voltage	[V]	10...55 DC
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open / normally closed; (selectable)
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	4
Max. leakage current	[mA]	0.6
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	50
Short-circuit protection		yes

KG5026



Capacitive sensor

KGE2008-FRKG/US-100-IRF/0LED

Type of short-circuit protection	pulsed
Overload protection	yes
Detection zone	
Sensing range [mm]	8
Real sensing range Sr [mm]	8 ± 10 %
Operating distance [mm]	0...6.5
Accuracy / deviations	
Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [X01]	1...15
Switch point drift [X01]	-15...15
Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 65
Tests / approvals	
EMC	EN 60947-5-2
Mechanical data	
Housing	threaded type
Mounting	non-flush mountable
Dimensions [mm]	M18 x 1
Thread designation	M18 x 1
Materials	PBT; end cap: PC
Аксессуары	
Items supplied	lock nuts: 2
	screwdriver: 1
Remarks	
Pack quantity	1 pcs.

KG5026



Capacitive sensor

KGE2008-FRKG/US-100-IRF/0LED

Electrical connection - plug

Connector: 1 x M12; coding: A

