


O1D108



Photoelectric distance sensor

O1DLF3KG/IO-LINK



- 1 alphanumeric display 4-digit
2 programming buttons



Product characteristics

Laser protection class	2
Housing	rectangular

Application

Application	[m]	0.2...100
-------------	-----	-----------

Electrical data

Operating voltage	[V]	18...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 150
Protection class		III
Reverse polarity protection		yes
Typ. lifetime	[h]	50000

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Electrical design	PNP
Number of digital outputs	2
Output function	normally open / normally closed; (programmable)
Max. current load per output [mA]	200



Photoelectric distance sensor

O1DLF3KG/IO-LINK

Number of analogue outputs	1
Analogue current output [mA]	4...20; (IEC 61131-2)
Max. load [Ω]	250
Analogue voltage output [V]	0...10; (IEC 61131-2)
Min. load resistance [Ω]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone	
Max. light spot width [mm]	25
Max. light spot height [mm]	25
Light spot dimensions refer to	18 m
Background suppression [m]	< 100

Measuring/setting range	
Measuring range [m]	0.2...18; (white paper 200 x 200 mm 90% remission)
Sampling rate [Hz]	1...33

Interfaces					
Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
SDCI standard	IEC 61131-9				
Profiles	Smart Sensor: Sensor Identification; Binary Data Channel; Process Value; Sensor Diagnosis				
SIO mode	yes				
Required master port type	A				
Process data analogue	2				
Process data binary	2				
Min. process cycle time [ms]	6				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>811</td></tr> </table>	Type of operation	DeviceID	default	811
Type of operation	DeviceID				
default	811				

Operating conditions	
Ambient temperature [°C]	-10...60
Protection	IP 67

Tests / approvals	
EMC	EN 60947-5-2
Laser protection class	2

O1D108



Photoelectric distance sensor

O1DLF3KG/IO-LINK

Notes on laser protection	Caution:	laser light
	Power:	$\leq 4,0 \text{ mW}$
	Wave length:	650 nm
	pulse:	1,3 ns
	Do not stare into beam.	
	Avoid exposure to the laser light.	
	laser class:	2
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
MTTF	[ANN]	106

Mechanical data

Weight	[g]	305
Housing		rectangular
Dimensions	[mm]	59 x 42 x 52
Materials		housing: diecast zinc; front pane: glass; LED window: PC
Lens alignment		side lens

Displays / operating elements

Display	switching status	2 x LED, yellow
	operation	LED, green
	distance value, programming	alphanumeric display, 4-digit

Аксессуары


Accessories (optional)	Protective cover, E21133
------------------------	--------------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection


Connector: 1 x M12; coding: A



Photoelectric distance sensor

O1DLF3KG/IO-LINK

Connection



2: OUT2 switching output or 4...20 mA / 0...10 V
 4: OUT1 switching output or IO-Link
 5: IN Laser On/ Off Ein / Aus

Other data

Parameter	Setting range	Factory setting
Uni	m, inch	m
OU1	Hno, Hnc, Fno, Fnc	Hno
SP1	0.20...18.00	1.00
nSP1	0.20...18.00	0.80
FSP1	0.20...18.00	1.20
OU2	Hno, Hnc, Fno, Fnc, I, U	I
SP2	0.20...18.00	2.00
nSP2	0.20...18.00	1.80
FSP2	0.20...18.00	2.20
ASP	0...18.00	0
AEP	0...18.00	18.00
rATE [Hz]	1...15	15
dS1	0...0.1...5	0
dr1	0...0.1...5	0
dS2	0...0.1...5	0
dr2	0...0.1...5	0
dFo	0...0.1...5	0
dIS	d1...3 ; rd1...3; OFF	d3

O1D108



Photoelectric distance sensor

O1DLF3KG/IO-LINK

repeatability/accuracy

	repeatability of the measured values		accuracy	
	white (90 % remission)	grey (18 % remission)	white (90 % remission)	grey (18 % remission)
0.20...1.0 m	± 0.45 cm	± 0.6 cm	± 1.5 cm	± 1.6 cm
1.00...2.00 m	± 0.5 cm	± 0.8 cm	± 1.5 cm	± 1.8 cm
2.00...4.00 m	± 1.25 cm	± 1.9 cm	± 2.25 cm	± 3.0 cm
4.00...6.00 m	± 2.0 cm	± 3.0 cm	± 3.0 cm	± 4.0 cm
6.00...10.00 m	± 3.5 cm	± 5.0 cm	± 4.5 cm	± 6.0 cm
10.00...18.00 m	± 5.0 cm		± 6.0 cm	

Sampling rate 15 Hz

Extraneous light on the object < 10 klx

The values apply at

constant ambient conditions 23 °C / 960 hPa

minimum power-on time in minutes 10

repeatability/accuracy

	repeatability of the measured values		accuracy	
	white (90 % remission)	grey (18 % remission)	white (90 % remission)	grey (18 % remission)
0.20...1.0 m	± 0.45 cm	± 0.6 cm	± 1.5 cm	± 1.6 cm
1.00...2.00 m	± 0.5 cm	± 0.8 cm	± 1.5 cm	± 1.8 cm
2.00...4.00 m	± 1.6 cm	± 1.9 cm	± 2.5 cm	± 3.0 cm
4.00...6.00 m	± 2.4 cm	± 3.3 cm	± 3.5 cm	± 4.5 cm
6.00...10.00 m	± 5.0 cm		± 6.5 cm	

Sampling rate 15 Hz

Extraneous light on the object < 40 klx

The values apply at

constant ambient conditions 23 °C / 960 hPa

minimum power-on time in minutes 10

In case of higher extraneous light on the object (up to 40 klx) the following specifications apply:

	white (90 % remission)	grey (18 % remission)	black (6 % remission)	
Measuring range	0.2...10 m	0.2...6 m	0.2...4 m	