




Capacitive NAMUR sensor

KI-2015-N/NI/6M/1D/1G



Product characteristics

Electrical design	NAMUR
Output function	normally closed
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 81

Electrical data

Connection to switching amplifiers	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC [V]	8.2; (1kΩ)
Supply voltage DC [V]	7.5...15
Current consumption [mA]	< 1; (disabled; conductive: > 2,2)
Protection class	II
Measuring principle	capacitive

Outputs

Electrical design	NAMUR
Output function	normally closed
Switching frequency DC [Hz]	40
Short-circuit proof	yes

Detection zone

Sensing range [mm]	15
Sensing range adjustable	yes
Factory setting sensing range [mm]	15
Real sensing range Sr [mm]	15 ± 10 %

Accuracy / deviations

Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [X01]	1...15
Switch point drift [X01]	-15...15

Operating conditions

Ambient temperature [°C]	-20...60
--------------------------	----------


KI5031



Capacitive NAMUR sensor

KI-2015-N/NI/6M/1D/1G

Protection	IP 65	
Tests / approvals		
Approval	DMT 01 ATEX E 020; TIIS TC15627; IECEx BVS 06.0003	
ATEX marking	 II 1G Ex ia IIB T6 Ga	
	 II 1D Ex ia IIIC T90°C Da	
EMC	EN 60947-5-2	
MTTF	[ANN]	841
Safety classification		
Max. internal capacitance	[nF]	375.64
Max. internal inductance	[μH]	3
Mechanical data		
Weight	[g]	378.5
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 81
Thread designation	M30 x 1.5	
Materials	PBT	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 6 m, PVC; 2 x 0.5 mm²		
Connection		



BN = Core colours :
brown
BU = blue